

PICCOLO PC F 65 G



Sample photo

Order symbol: PC F 65 G
Product nbr: 8724311
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002198
EI. number:
 Finland: 3423413
 Electric No. Denmark: 8212001611
 Electric No. Italy: 7201040
 Electric No. Sweden: 2536820

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	230	80	65	FM-3 FP 22040
inch:	9.1	3.1	2.6	DIN-35 Mounting rail Wall fastening lug (2 pcs)

Materials:	Rating:
Material: Polycarbonate	Ingress Protection (EN 60529): IP66/IP67
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Grey	UV resistance: UL 508
Gasket material: Polyurethane	Flammability Rating: UL 746C 5"
	Glow Wire Test (IEC 695-2-1) °C: 960
	NEMA Class: NEMA 1, 4X, 6, 12, 13

Temperatures:	Certificates:
Temperature °C (short term): -40 ... 120 °C	SGS Fimko
Temperature °C (continuous): -40 ... 80 °C	
Temperature °F (short term): -40 ... 250 °F	
Temperature °F (continuous): -40 ... 175 °F	

Accessories:
F-MP Mounting plate

