

PSEN 2.1-20/1actuator

512120



Actuator for magnetic safety switch, square design, IP6K9K, operating distance depending on the actuator 8/12 mm, height design 13 mm, PU = 1 actuator.

Technical details

General data

Approval:	CE, UKCA, cULus Listed, EAC (Eurasian), TÜV, ECOLAB
unit type:	Actuator

Technical data

Environmental data

ATEX category:	II 3GD EEx nC IIC T6
Ambient temperature:	-25 - 70 °C
Max. ambient temp. at 2000 m:	+70 °C
Perm. operating height ASL:	4000 m
Vibration to standard:	EN 60947-5-2
Acc. shock to standard1:	30g
Pollution degree clear.&creep.:	3


Mechanical data

Housing material upper part:	PBT
Height dimension:	36 mm
Width dimension:	26 mm
Depth dimension:	13 mm
Net weight:	17 g
Gross weight:	18 g

Environment

RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548026726
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274002
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0 dm3

Optional accessories



540310

PSEN screw M4x16 10pcs



534310

PSEN Distanzplatte / spacer (10 pcs.)



533111

PSEN Kabel Gerade/cable straightplug 2m



532110

PSEN Winkel / bracket



534320

PSEN reverse spacer



533110

PSEN Kabel Winkel/cable angleplug 2m



533121

PSEN Kabel Gerade/cable straightplug 5m



533120

PSEN Kabel Winkel/cable angleplug 5m



533131

PSEN Kabel Gerade/cable straightplug 10m



533130

PSEN Kabel Winkel/cable angleplug 10m



533141

PSEN Kabel Gerade/cable straightplug 30m



533140

PSEN Kabel Winkel/cable angleplug 30m



380200

PSS67 Cable M8sf M12sm, 3m



380203

PSS67 Cable M8sf M12sm, 30m



380204

PSS67 Cable M8af M12sm, 3m



773600

PDP67 F 8DI ION



380300

PSEN ma adapter



380201

PSS67 Cable M8sf M12sm, 5m



380202

PSS67 Cable M8sf M12sm, 10m



380207

PSS67 Cable M8af M12sm, 30m



380205

PSS67 Cable M8af M12sm, 5m



380206

PSS67 Cable M8af M12sm, 10m