



182.72.104.66HFLHülsenfreiläufe

Drawn cup roller clutches HFL3530 (Series HFL)

with plain or rolling bearing arrangement, steel springs

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

F _w	35 mm
D	42 mm
C	30 mm Tolerance: 0/-0,3
r _{min}	0,3 mm
Drawn cup roller clutches with rolling bearing arrangement.	
m	58 g Mass
M _d per	121 Nm Permissible torque
n _{GW}	3900 1/min Limiting speed with rotating shaft (valid for grease and oil lubrication)
n _{GA}	3900 1/min Limiting speed with rotating outer ring (valid for grease and oil lubrication)
C _r	12200 N Basic dynamic load rating, radial
C _{0r}	18800 N Basic static load rating, radial
C _{ur}	2550 N Fatigue limit load, radial

