

# CZS240



COPPER CRIMP LINK - 240SQMM



Product image  
not available

## General Information

Extended Product Type	CZS240
Product ID	7TBH007500R0060
EAN	5415022198041
Catalog Description	COPPER CRIMP LINK - 240SQMM
Long Description	Australian Standard Series Copper Bell Mouth Lug - Cable 35 millimeters squared, Stud Size M12

## Ordering

EAN	5415022198041
Minimum Order Quantity	300 piece
Customs Tariff Number	8536904000

## Dimensions

Product Net Weight	0.454 kg
--------------------	----------

## Container Information

Package Level 2 Units	300 piece
Package Level 2 Width	25.4 mm
Package Level 2 Height	25.4 mm
Package Level 2 Depth / Length	25.4 mm
Package Level 3 Units	300 piece

## Additional Information

Brand / Label	Color-Keyed
Insulation Material	None
Material	Copper
Product Main Type	COMPRESSION CONNECTORS
Product Name	COPPER LUG
Product Type	Metric Splice
UPC	786209805539

## Certificates and Declarations (Document Number)

---

Data Sheet, Technical Information	CZS240
Instructions and Manuals	CZS240

---

---

## Classifications

---

ETIM 6	EC001059 - Crimp splices for copper conductor
UNSPSC	39121449
WEEE Category	Product Not in WEEE Scope

---

---

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors



Product image  
not available