

55

Farriers' Pincers

(Tear-off Pliers for vehicle bodywork)

DIN ISO 5743



55 00 300



- the ideal pliers for the farrier
- with small head and anvil for redirecting horseshoe-nails
- also suitable for dismantling work in vehicle body workshops
- cutting edges additionally hardened; cutting edge hardness approx. 59 HRC
- Special tool steel, forged, oil-hardened



Article No.	EAN 4003773-	↔ mm		Pliers	Head	Head width mm	g
55 00 300	014072	300		black atramentized	polished	20,0	786

57

Unsoling Pincer for horseshoes

DIN ISO 5743



57 00 360



- for the farrier
- also suitable for dismantling work in vehicle body workshops
- also for dismantling work on timber and metal
- cutting edges additionally hardened; cutting edge hardness approx. 59 HRC
- Special tool steel, forged, oil-hardened

Article No.	EAN 4003773-	↔ mm		Pliers	Head	Head width mm	g
57 00 360	017622	360		black atramentized	polished	30,5	1164

58

Potters' Pincers (Brick Pincers)

DIN ISO 5743



58 30 225



- for pottery work
- with wire cutter for soft wire
- cutting edges additionally hardened; cutting edge hardness approx. 59 HRC
- Special tool steel, forged, oil-hardened

58 10 225
head width 10 mm

58 30 225
head width 20 mm

Article No.	EAN 4003773-	↔ mm		Pliers	Head	Head width mm	g
58 10 225	017646	225		black atramentized	polished	10,0	328
58 30 225	014331	225		black atramentized	polished	20,0	347

