

18V CHAINSAW 250mm BL LXT DUC254Z

18V LXT BL Top Handle Chainsaw

To be used by trained tree surgeons only!



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Chain Oil Capacity	140 ml (cm ³)
Chain Gauge	0.043 "
Chain Pitch	3/8 "
Chain Speed	0 - 24 m/sec
Bar Size	25 cm
Noise sound pressure	92.2 dB(A)
Noise sound power	103.2 dB(A)
Noise K factor	2.5 dB(A)
Maximum Output	570 w
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	3.1 m/sec ²
Net weight	2.8 - 3.3 kg

USER BENEFITS

- Variable speed control by trigger
- Soft start
- Electric chain brake
- Kickback brake
- Chain oil adjustment
- Oil Capacity Display
- Brushless motor
- Compact & Lightweight.
- Captive nuts: prevent loss of nut when removing sprocket cover to replace guide bar or saw chain
- Hanging hook
- Main power switch with auto power-off function

[Link to product - makitauk.com](https://www.makita.com)



RELATED PRODUCTS

(Recon

■ OTHER