

tesaflex® 4163 Multipurpose Soft PVC Premium

tesaflex® 4163 permits is a special formulated Soft PVC tape with a good film flexibility. Due to the UV stable acrylic adhesive it is perfect suitable for permanent applications.

Main Application

tesaflex® 4163 is universal useable and exceptionally qualified for general jobs like:

- Installation
- Repairing
- Marking
- Splicing
- Bundling

Technical Data

▪ Backing material	soft PVC	▪ Tensile strength	30 N/cm
▪ Total thickness	130 µm	▪ Temperature resistance	105 °C
▪ Type of adhesive	acrylic	▪ UV-resistance	104 weeks
▪ Adhesion to steel	1.8 N/cm	▪ Dielectric breakdown voltage	7000 volt
▪ Elongation at break	250 %		

Properties

- Certified according to US 302

Additional Information

It conforms to US safety standard 302. The isogenogrey colour is perfect suitable for instalation of water pipes.

For latest information on this product please visit <http://l.tesa.com/?ip=04163>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.