

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
Article No.	114951
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	Yellow/Transparent
Finish	Matt
Order Reference	M71-21-427-YL
Printable Area - Height (mm)	19.05
Printable Area - Width (mm)	25.40
Printer Compatibility	BMP71
Size - Height (mm)	63.50
Size - Width (mm)	25.40
Additional Information	Self-Laminating;Self-Extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	100 Label(s) / Box
Vertical Repeat (mm)	66.68
Wire Gauge	3 to 0000
Approval/Compliance	UL Recognised
Ribbon Series	M71-R4300
Application	Laboratory Identification; Voice & Data Communication; Wire & Cable Marking
Environment	Freezer; Liquid Nitrogen
Industry	Aerospace;Data/Telecommunications;Defence;Electrical;Electronics;Healthcare;Laboratory;Mas Transit;
Laboratory Application	Straws
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL Approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Characters per Line	24
Max. Lines of Text	8
Max. Service Temp. °C	60
Max. Wire/Cable	14.20

