



**Low Profile  
T&B Catalog Number:**

SF200-18X-100

**UPC Number:**

78621019178

**Status:**

Active

**Description:**

Cable Tie 18lb 8" Blk Low-Profile 1-Pc

**Features**

Low-Profile, contoured head reduces clearance required for the bundle and enhances the appearance of your harness.

The safeguard wall eliminates exposure to sharp edges.

The saddleback fits snug against the contour of the wiring harness.

**General**

Material Nylon 6.6 Weather Resistant

Color Black

**Dimension Information**

Nominal Length (inches) 8

Length (inches) 8.1

Width (inches) 0.095

Max. Wire Bundle Diameter (inches) 2

Min. Wire Bundle Diameter (inches) 0.125

Thickness (inches) 0.043

**Specifications**

Temperature Rating -40°F to 185°F

Flammability Rating UL 94 V-2

**Packaging**

T&B Order Multiple 100

T&B Inner Pack 100

Package in Units 1000

Package Type Regular

T&B Sold in UOM Each

T&B Weight Per UOM 1.88 lbs. per 1000

**Application Support**

Overview Available on Website

Material Selection Guide Available on Website

**Certifications**

RoHS Compliance Yes

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com