

# UniBond

## Duct Tape

Issued: 24-May-10

Ref: UT3000

Product Description	Typical Technical Data	Application
<p>Heavy duty, strong, tough and 100% weatherproof*, multi-purpose cloth tape.</p> <p><b>Carrier:</b> Polyethylene reinforcement with polyester fabric scrim.</p> <p><b>Adhesive:</b> Extra high strength synthetic rubber.</p>	<p><b>Colours:</b> Silver, black, white, orange</p> <p><b>Thickness:</b> 220 µm</p> <p><b>Width:</b> 50mm</p> <p><b>Tensile Strength (N/cm):</b> 45</p> <p><b>Elongation at break (%):</b> 25</p> <p><b>Peel adhesion (N/cm):</b> 17</p> <p><b>Unwind force (N/cm):</b> 3</p> <p><b>Temperature range °C:</b> -5 to + 60</p>	<p>Hundreds of uses around the home, garden, garage and workplace.</p> <p>Fixes, binds, mounts, repairs, bundles, joins, seals, reinforces, protects and identifies.</p> <p>Suitable for interior and exterior use.</p> <p>Easy to tear by hand.</p> <p><b>Limitations:</b> Not intended for permanent repairs. Not suitable for use on glass. *Not suitable for total immersion in water, e.g. pond liners, children's pools.</p>

*The above data and performance characteristics are compiled on the results of tests and estimates based on careful calculations. They are put forward in good faith but are not guaranteed. In particular the customer should satisfy himself of the suitability of the product for its intended use and consult us if he is in any doubt about any particular application.*

*The conditions under which this product is stored affect its performance. Storage should be in dry well ventilated rooms with a reasonably consistent temperature around 20°C and protected from continuous exposure to direct sunlight. The product should always be applied to clean dry surfaces.*