


LR5207-X-2Z-TVH-XL

Galet de roulement

Yoke type track rollers LR52..-2Z-TVH-XL, double row self-retaining angular contact ball bearings with particularly thick-walled outer ring, ball and cage assembly and an inner ring, axial guidance of outer ring is provided by the balls, lubrication hole in inner ring on request, sealing shield on both sides, cage made from glass fibre reinforced polyamide, X-life design

Information technique



Votre alternative produit actuelle

joint	2Z	Déflecteur des deux côtés
profile bague extérieure	X	Diamètre extérieur cylindrique
dispositif de lubrification	Without	Without
Cage	TVH	Cage polyamide renforcée fibre de verre

dimensions principale & données de performance

D	80 mm	Diamètre extérieur
d	35 mm	Alésage
C	27 mm	Hauteur
$C_{r\,w}$	32.500 N	Charge dyn. de base, radiale
$C_{0r\,w}$	27.500 N	Charge stat. de base, radiale
$C_{ur\,w}$	1.450 N	Limite à la fatigue, radiale
$n_{D\,G}$	4.650 1/min	Vitesse pour une lubrification à la graisse
$F_{r\,per}$	22.200 N	Charge radial dynamique admissible sur bague extérieure
≈m	0,66 kg	Poids

Dimensions

d_2	47 mm	Diamètre rondèle de butée
r_{min}	1,1 mm	Dimension minimum de chanfrein
R	500 mm	Rayon bague extérieure profile externe

La fiche technique ne contient qu'une vue d'ensemble des données techniques du produit sélectionné. Reportez-vous à la documentation supplémentaire pour ce produit. Pour plus d'informations, vous pouvez utiliser le lien suivant sur notre site Web : Formulaire de contact