

EchoMax XPS-15 Ultrasonic level transducer: continuous, non-contact, 15 m (49.21 ft), for liquids and solids. Mounting thread and facing: R 1" ((BSPT) EN 10226-1) Cable length: 5 m (16.40 ft) Mounting flange: None Approvals: ATEX II 2GD Ex mb IIC T4 Gb, ATEX II 2GD Ex tb IIIC T135°C Db, Ta = -40°C to +95°C; UKEX II 2GD Ex mb IIC T4 Gb, UKEX II 2GD Ex tb IIIC T135°C Db, Ta = -40°C to +95°C; IECEx SIR 13.0009X Ex mb IIC T4 Gb IECEx SIR 13.0009X Ex tb IIIC T135°C Db, Ta = -40°C to +95°C; FM Class I, Div. 2, Groups A, B, C, D; FM Class II, Div. 1, Groups E, F, G; FM Class III Manual: Multi-Language,Quick Start

Further information

Industry Online Support (Manuals, Catalogs, Certificates, FAQ, ...)

<https://support.industry.siemens.com/cs/products?mfn=ps&lc=en-WW>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>

