



182.72.104.66NKNadellager

Needle roller bearings NK26/20-XL

(Series NK)

light series

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	26 mm
D	34 mm
C	20 mm
rmin	0,3 mm
m	42 g Mass
Cr	22000 N Basic dynamic load rating, radial
C0r	32000 N Basic static load rating, radial
Cur	5600 N Fatigue limit load, radial
nG	17200 1/min Limiting speed
nB	10100 1/min Reference speed
	G26X34X4 Suitable sealing ring
	SD26X34X4 Suitable sealing ring

