

Rigid Steel Rules, Left to Right

Stainless Steel Rules

Accuracy class acc. to tolerance class II

• reading from left to right

- semi rigid version, with wide cross section
- stainless spring steel
- non glare, matt surface
- etched graduation for a clear reading

type A = mm / mm top and bottom 1/1 mm graduation

type B = ½ mm / mm top ½ mm and bottom 1/1 mm graduation

type D = inch / mm top ½ mm and 1/1 mm
bottom 1/64 ; 1/32 and 1/16 inch graduation,

Numbering up to 500 mm length with continuing mm numbering at type A and type B.
The rules from 1000 mm up to 4000 mm length with continuing cm numbering at type A and type B.
The rules up to 4000 mm length according to tolerance class II are qualified as reference pieces.
Therefore please order our calibration certificate together with the rule.
Steel Rules more than 4000 mm length are made according to workshop standard.

type A



type B



type D



INOX

II

CE

ART No

type A	type B	type D	 mm		
1018010030	1018020030	1018040030	300	30 x 1	on request
1018010050	1018020050	1018040050	500	30 x 1	on request
1018010060	1018020060	1018040060	600	30 x 1	on request
1018010100	1018020100	1018040100	1000	30 x 1	on request
1018010150	1018020150	1018040150	1500	30 x 1	on request
1018010200	1018020200	1018040200	2000	30 x 1	on request
1018010300	1018020300	1018040300	3000	30 x 1	on request
1018010400	1018020400	1018040400	4000	30 x 1	on request
1018010500	1018020500	—	5000	30 x 1	on request
1018010600	1018020600	—	6000	30 x 1	on request
1018010700	1018020700	—	7000	30 x 1	on request
1018010800	1018020800	—	8000	30 x 1	on request
1018010900	1018020900	—	9000	30 x 1	on request
1018011000	1018021000	—	10000	30 x 1	on request
1018011100	1018021100	—	11000	30 x 1	on request
1018011200	1018021200	—	12000	30 x 1	on request
1024010050	1024020050	1024040050	500	40 x 2	on request
1024010100	1024020100	1024040100	1000	40 x 2	on request
 1024010150	 1024020150	 1024040150	1500	40 x 2	on request
 1024010200	 1024020200	 1024040200	2000	40 x 2	on request