





US40-XX-XX-SS-KIT

Ruland US40-XX-XX-SS-KIT, Machinable Bore Single Universal Joint Kit, Friction Bearing, Stainless Steel, 2.495" (63.4mm) OD, 7.000" (177.8mm) Length



Description

Ruland US40-XX-XX-SS-KIT is a single cardan friction bearing universal joint kit that can be machined with a bore size and geometry of the user's choice. It has a 2.495" (63.4mm) OD and 7.000" (177.8mm) length. US40-XX-XX-SS-KIT is ideal for applications with space constraints and has higher torque capacity than equivalently sized double universal joints. This plain bearing universal joint is comprised of pins and blocks that are precision machined, selectively heat treated, and ground for high strength, accuracy, and wear resistance. The combination of these components with precision ground and hardened yoke ears allow for a longer lifespan, increased performance in demanding applications, and greater angular misalignment of up to 45° when compared to commodity style single universal joints. US40-XX-XX-SS-KIT is made from high grade stainless steel for increased corrosion resistance. It can be combined with boot UBOOT40/64-NI-KIT to protect the joint from unwanted contaminants such as dust or water and self lubricate reducing maintenance time. This single cardan universal joint is manufactured in the USA by Belden Universal for strict control of processes.

Product Specifications

Bore (B1)	No Bore	Small Bore (B2)	No Bore
B1 Max Shaft Penetration	2.090 in (53.1 mm)	B2 Max Shaft Penetration	2.090 in (53.1 mm)
Joint Outer Diameter (OD)	2.495 in (63.4 mm)	Length (L)	7.000 in (177.8 mm)
Yoke Length (LY)	3.500 in (88.9 mm)	Hub Depth (LH)	2.090 in (53.1 mm)
Max Round Bore (Inch)	1.4375 in	Max Round Bore (Metric)	36 mm
Max Hex or Square Bore (Inch)	1.2500 in	Max Hex or Square Bore (Metric)	35 mm
Max Blind Bore (Inch)	2.0000 in	Max Blind Bore (Metric)	50 mm
Max Round Bore w/ Key (Inch)	1-1/2" Bore, 3/8" Keyway	Max Round Bore w/ Key (Metric)	38mm Bore, 10mm Keyway
Rated Torque	4,650 in-lb (525.4 Nm)	Max Operating Angle	45°
Material Specification	Yokes: 303 Stainless Steel Pins and Blocks: 416 Stainless Steel	Manufacturer	Belden Universal
Country of Origin	USA	Weight (lbs)	8.219000
Recommended Lubricant	LUBRIPLATE No. 1200-2	Matching Boot Cover	UBOOT40/64-NI-KIT
UPC	63452929003	Tariff Code	8483.60.4000
UNSPC	25173810		
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	⚠ WARNING This product can expose you to the chemical Nickel (metallic), known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov .		