


Fiche technique produit

LUHR 12

Unité de roulements linéaires sans joints



A [mm]:	28
D = Da [mm]:	19
Fw [mm]:	12
H [mm]:	17
H1 [mm]:	33
H2 [mm]:	16
H3 [mm]:	11
J [mm]:	29
L [mm]:	40
N [mm]:	4.3
N1:	M5
Rangées de billes [#]:	5
Cdyn [N]:	695

Date 21/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

Fiche technique produit

LUHR 12

Unité de roulements linéaires sans joints

C0 [N]:	510
Masse [kg]:	0.08
A1[mm]:	35
C1[mm]:	34

Date 21/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.