

FEATURES

- **UV Resistant:** Ensures durability and performance in outdoor environments
- **Nylon Material:** Offers strength and flexibility for secure cable bundling
- **Tensile Strength of 34 kg:** Provides robust holding capacity for heavy-duty applications
- **Maximum Bundle Diameter of 94 mm:** Accommodates larger cable groups for versatile use
- **Fire Behaviour UL 94 V-2:** Meets safety standards for flame retardancy
- **Operating Temperature up to 85 °C:** Suitable for use in a variety of temperature conditions

RS PRO UV Protected Cable Tie, 368 mm Length

RS Stock No: 656-043



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO UV Protected Cable Tie is designed for securing and organising cables in various environments. With a length of 368 mm, it is ideal for bundling larger cable groups, providing a reliable and durable solution for cable management. Its UV resistance makes it suitable for outdoor use, ensuring longevity and performance in sunlight-exposed areas.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	UV Protected Cable Tie
Tensile Strength	34 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	368 mm
Material	Nylon
Maximum Bundle Diameter	94 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---