suction cup VASB-75-1/4-NBR Part number: 35415

With sealing ring OL.

FESTO





Data sheet

Feature	Value	
Nominal size	4 mm	
suction cup diameter	75 mm	
Effective suction diameter	60 mm	
Position of connection	on top	
Suction cup shape	Round, bellows 1.5 conv	
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]	
Ambient temperature	-20 80 °C	
Breakaway force at 70% vacuum	197 N	
Retention force at nominal operating pressure	197 N	
Mounting thread	G1/4	
suction cup mounting	G 1/4	
Vacuum connection	G1/4	
Colour	Black	
Shore hardness	60 +/- 5	
Material of threaded plug	Zinc die-casting	
Materials note	Conforms to RoHS	
Material suction cup	NBR	