
**PASEY15-XL** **Plummer block housing unit**

Plummer block housing units PASEY, cast iron housing, radial insert ball bearing with grub screws in inner ring, P seals

X-life**Technical information****Your current product variant**

Material	GG	Grey cast iron
----------	----	----------------

Main Dimensions & Performance Data

d	15 mm	Bore diameter
L	125 mm	Length total
H 2	57 mm	Height
≈m	0.41 kg	Weight

Mounting dimensions

J	95 mm	Distance fixing bore
N	11 mm	Width (slot)
N 1	19 mm	Length (slot)

Dimensions

H	30.2 mm	Distance shaft axis
A	30 mm	Width (base)
A 1	18 mm	Width (head)
H 1	10 mm	Height (base)
B	22 mm	Width
S 1	16 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication



Additional information

ASE03	Housing
GAY15-XL-NPP-B	Bearing designation

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.