

Eaton 160MJ31-7

Catalog Number: 160MJ31-7

Eaton Bussmann series low voltage british standard fuse, 160A, AC 415 V, V88/J, 31 x 131 mm, gU, 92mm fixing centres, type 7



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage british standard fuse	160MJ31-7
	EAN
	5027590437134
Product Length/Depth	Product Height
160 mm	65 mm
Product Width	Product Weight
140 mm	234.1 g
Compliances	Certifications
CE Marked	BS
RoHS Compliant	IEC 60269
	EAC

Electrical data

Amperage Rating

160 A

Voltage rating

415 V

Voltage type

AC

Breaking capacity

80 kA

Class

Class gG/gL

Product specifications

Application

feeder pillars

Fuse type

MJ31

Fitted with:

Slotted tags

Connection

Bolt-on

Resources

Catalogs

[CA134002EN](#)

Declarations of conformity

[UKCA Feeder pillar fuse-links](#)

[CE Feeder pillar fuse-links](#)

Multimedia

[Eaton Bussmann - Red Spot fuse links](#)

Technical data sheets

[4180 MJ31 fuses and 92AL fuses](#)

Technical service bulletins

[Datasheet - 160MJ31-7](#)