
Parker Product Datasheet



Quick coupling system with nominal diameter 7.2 for pneumatic applications up to 35 bar. Available in brass sleeve or polymer.

PART NUMBER: 26SRTF09MXX
COUPLING HALF: Plug
BODY MATERIAL: Brass
FUNCTION: Recoil Eliminator
CONNECTION TYPE: Hose Barb
CONNECTION SIZE: 9 MM

PRODUCT OVERVIEW

Parker's Basic Quick Coupling Series 26 is an industrial brass coupling with European profile. Coupling system with single-hand operation and standard-valve. Small mass size. The ergonomic sleeve (available in Brass or Polymer) design prevents dirt on the valve body.

Markets:
- General Industrial
- Industrial manufacturing equipment

Features/Benefits:
- Industrial coupling with European profile, most representative profile worldwide
- Single-hand operation for easy and fast connection

TECH SPECIFICATIONS

APPLICATION	Trucks & Trailers
CONNECTION TYPE	Hose Barb
DIVISION	Low Pressure Connectors Europe Division
APPLICATION	Food & Beverages
VALVE TYPE	Without Valve
PRODUCT STYLE	Quick-Connect
COMPATIBLE FITTING	Series 26 Coupler
FUNCTION	Recoil Eliminator
SEAL MATERIAL	Without Seal
APPLICATION	Mobile & Defence
TECHNOLOGY	Pneumatics
PLATING TYPE	Without Surface Treatment
DIVISION	Low Pressure Connectors Europe Division
QUANTITY PER BOX	10
APPLICATION	Industrial Machinery
PRODUCT TYPE	Pneumatic Quick Couplings
OPERATION TYPE	No Sleeve
APPLICATION	Air & Gas Compressor
SLEEVE MATERIAL	Without Sleeve
REGION OF ORIGIN	Germany
COUPLING HALF	Plug
FLOW RATE	1070 L/min (air)
MINIMUM OPERATING TEMPERATURE	-40 °F
DIAMETER	7.2 mm (nominal)
LENGTH	60 mm
INDUSTRY	General Industrial

MAXIMUM OPERATING PRESSURE	507 psi
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air)
BRAND	Rectus
MAXIMUM OPERATING TEMPERATURE	392 °F
VALVE INCLUDED	No
WEIGHT	0.0447 kg
INDUSTRY	Transportation
MAXIMUM OPERATING TEMPERATURE	200 °C
BRAND	Parker
MINIMUM OPERATING TEMPERATURE	-40 °C
CONNECTION SIZE	9 mm
INTERCHANGE TYPE	European Profile
PRODUCT SERIES	Series 26
MAXIMUM OPERATING PRESSURE	35 bar
INDUSTRY	Healthcare & Life Sciences
BODY MATERIAL	Brass
HEX SIZE	21 mm
APPLICATION	Safety & Rescue