



### Main

Range	Merten
Product name	Merten insert
Product or component type	R-TV/SAT socket
Device application	Media device support
Device presentation	Mechanism with fixing frame

### Complementary

Socket number	2
TV socket type	Intermediate
Transmission frequency	4...2400 kHz
Path attenuation	2.5 DB 860 kHz 3.5 dB 2400 kHz
Tap loss	10 at 2150 kHz 10 at 860 kHz
Device mounting	Flush
Fixing mode	By screws and claws

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Minimum percentage of recycled plastic content	0