



182.72.104.66NKX..-ZNadel-Axialkugellager

Needle roller/axial ball bearings

NKX17-Z-XL (Series NKX..-Z)

axial component, single direction, to DIN 5429, with end cap, for grease lubrication

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	17 mm
D	26 mm
C	25 mm Tolerance: 0/-0,25
C1	9 mm Tolerance: 0/-0,2
C2	8 mm
D2 max	31,2 mm
da	25,7 mm
dw	17 mm Tolerance: E8
ra max	0,3 mm
rmin	0,3 mm
	NAXK17Z Designation to DIN 5429
m	55 g Mass
Cr	13500 N Basic dynamic load rating, radial
C0r	15000 N Basic static load rating, radial
Ca	10800 N Basic dynamic load rating, axial
Coa	18200 N Basic static load rating, axial
Cur	2750 N Fatigue limit load, radial
Cua	870 N Fatigue limit load, axial
ng	8500 1/min Limiting speed
	IR14X17X17-XL Suitable inner ring

