




**Part Number :** [1062836339](#)

**Product Description :** QSFP-DD MPO-to-(8) LCD Uniboot Jumper Cable Assembly, 50/125µm, 3.00mm, MultiMode, 16 Fiber, OM4, 5.0m Length, Aqua Cable

**Series Number :** 106283

**Status :** Active

**Product Category :** Fiber Optic Cable Assemblies



---

## Documents & Resources

### Drawings

[1062836339\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106283
Description	QSFP-DD MPO-to-(8) LCD Uniboot Jumper Cable Assembly, 50/125µm, 3.00mm, MultiMode, 16 Fiber, OM4, 5.0m Length, Aqua Cable
Connector to Connector	MPO/APC-to-(8) LCD Uniboot
Keyword	16F
Mode	Multimode
Product Name	MPO,QSFP-DD Optical Cables,LCD Uniboot
UPC	196823414220

### Agency

CSA	LR64395
UL	E72548

### Physical

Boot Type	Straight
Cable Length	5.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	1.000/g
Single Ended	No
Wire/Cable Type	16 Fiber OM4 Plenum