

1.04/ST-HP-B

Puller-Set

with stand

Code	ETIM
2300044	EC011834
EAN	UNSPSC
4036976125320	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-15-01
Customs tariff number	
82055980	



Article description

- Consisting of 3 pullers in different sizes
- Cross-beam especially hardened and tempered allows safe application of extremely high pulling forces and doubles the tensile force capability
- Strong drop forged pattern
- Puller hook forged from one piece
- With leg brake - prevents unintentional leg slipping. The leg can be slid along the cross-beam at the push of a button
- Can be used as external and internal puller by repositioning the legs
- Scale for uniform adjustment of the puller legs. Allows centred pulling, with optimised application of force, even when extremely high pulling forces are required
- Can be retrofitted with hydraulic spindle

Article parts list

1.04/HP1A-B Puller HIGH POWER 2-arm 130x100 mm, 1.04/HP2A-B Puller HIGH POWER 2-armed 200x150 mm, 1.04/HP3A-B Puller HIGH POWER 2-armed 350x200 mm, 1.04/97 Stand empty for 1.04 series

Article information

Contents (Qty of pieces)	3	Quick release lever available	no
Total length [mm]	125 mm	3D data available	no
Graduation	yes	Spindle anti-slip device	no
reversible arms available	yes	Screws included	no
Clamping bracket available	no	Anti-slip device on the spindle	no
Net weight [kg]	14,4 kg	Exchangeable spindle tip	no
Hook brake available	yes	Can be retrofitted with hydraulic spindle	yes
Hook can be moved parallel	no		