

SACC-FPF-F-M12/M16 THR PPI - Housing screw connection



1233777

<https://www.phoenixcontact.com/gb/products/1233777>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 push-pull housing screw connection for M12 socket inserts, with molded seal

Your advantages

- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Flexible PCB assembly: two-piece connectors for wave and THR soldering

Commercial data

Item number	1233777
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQAAJ
Product key	ABQAAJ
GTIN	4063151335991
Weight per piece (including packing)	12.8 g
Weight per piece (excluding packing)	11.655 g
Customs tariff number	74198090
Country of origin	DE

SACC-FPF-F-M12/M16 THR PPI - Housing screw connection



1233777

<https://www.phoenixcontact.com/gb/products/1233777>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	If necessary, order locking nut separately

Product properties

Product type	Panel mounting base
Thread type	M12

Connection data

Connection method	THR solder connection
Tightening torque	2 ... 3 Nm

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
	FKM
Material of grip body	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated

Connector

Connection 1

Head design	Socket
Head thread type	M12
Head locking type	Push-pull internal locking

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP65/IP67 (correctly plugged in and locked)
Degree of protection	IP65/IP67 (correctly plugged in and locked)
	IP67, when in locked state
	IP65, when in locked state
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)

1233777

<https://www.phoenixcontact.com/gb/products/1233777>

UL Type Rating	Type 4 (indoor use only)
----------------	--------------------------

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	based on IEC 61076-2-010

Mounting

Mounting type	Front mounting M16
---------------	--------------------

SACC-FPF-F-M12/M16 THR PPI - Housing screw connection



1233777
<https://www.phoenixcontact.com/gb/products/1233777>

Classifications

ECLASS

ECLASS-13.0	27440224
-------------	----------

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-FPF-F-M12/M16 THR PPI - Housing screw connection



1233777

<https://www.phoenixcontact.com/gb/products/1233777>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk