

HOSE COILS

STOFLEX anti-static rubber hose - Coil



Part number	Length (m)	Radius of curve (mm)	Max. operating pressure (bar)	Net weight (Kg)	Color
STOFLEX 8	50.00	30.00	20.00	0,171	Blue
STOFLEX 9	50.00	35.00	20.00	0,179	Blue
STOFLEX 10	50.00	40.00	20.00	0,235	Blue

Part number	Ø int/ext (mm)
STOFLEX 8	8.00 / 15.00
STOFLEX 9	9.00 / 16.00
STOFLEX 10	10.00 / 18.00