

Pactec Part Number Identification Table

RS Part No.	Product Ref	Manu. Part No.
257-0680	72868-510-000	CNS-0000 (Black)
257-0747	73091-510-000	CNM-0000 (Black)
257-0775	73093-510-000	CNM-0103 (Black)
257-0753	73093-510-039	CNM-0103 (PC Bone)
257-0797	73095-510-000	CNM-0303 (Black)
257-0832	73096-510-039	CNM-0607 (PC Bone)
257-0860	73104-510-000	CNL-0000 (Black)
257-0927	73107-510-000	CNL-0407 (Black)
257-0911	73107-510-039	CNL-0407 (PC Bone)
257-0905	73108-510-000	CNL-0303 (Black)
257-0955	73109-510-039	CNL-0607 (PC Bone)
257-0696	73395-510-039	CNS-0006 (PC Bone)
257-0949	73516-510-000	CNL-0606 (Black)
257-0882	74016-510-000	CNL-0006 (Black)
257-0810	74796-510-000	CNM-0606 (Black)
257-0703	81737-510-000	CNS-0006 (Black)
257-0876	81742-510-039	CNL-0006 (PC Bone)