

LONG LIFE CUTTING METAL

PRO

- 1 Robust aluminium oxide grains for long-lasting performance
- 2 Resin matrix for strength and resistance to heat
- 3 Strong fibreglass net reinforces the disc



BOSCH

PRO METAL BONDED CUTTING DISC

PRO


- For cutting metal in general metalworking applications
- Highly efficient for metalworkers: Long Life
- Designed for cutting metal
- Click it on with X-LOCK or use it with nut and thread angle grinders



PRODUCT PROPERTIES						ORDERING INFORMATION					
Specification	Diameter mm	Bore diameter mm	Thickness mm	X-LOCK	oSa	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number	
Straight											
A 46 S BF	115	22.23	1.6	●	●	U0	1	25	947 428	2 608 619 252	
A 30 S BF	115	22.23	2.5	●	●	U0	1	25	947 435	2 608 619 253	
With depressed centre											
A 30 S BF	115	22.23	2.5	●	●	U0	1	25	947 466	2 608 619 256	
Straight											
A 30 S BF	115	22.23	2.5	●	-	U0	1	25	236 203	2 608 619 780	
With depressed centre											
A 30 S BF	115	22.23	2.5	●	-	U0	1	25	236 210	2 608 619 781	
Straight											
A 46 S BF	125	22.23	1.6	●	●	U0	1	25	947 442	2 608 619 254	
A 30 S BF	125	22.23	2.5	●	●	U0	1	25	947 459	2 608 619 255	
With depressed centre											
A 30 S BF	125	22.23	2.5	●	●	U0	1	25	947 473	2 608 619 257	
Straight											
A 30 S BF	125	22.23	2.5	●	-	U0	1	25	236 227	2 608 619 782	
With depressed centre											
A 30 S BF	125	22.23	2.5	●	-	U0	1	25	236 234	2 608 619 783	


BOSCH