



RevNo	Revision note	Date	Signature	Checked
1				
2				
3				



1.768±0.15
0.700
0.175
*Total 0.893±0.15
Excluding protective film



NOTES:

1. DISPLAY TYPE:5.48",1080*1920
2. DISPLAY MODE: AM OLED
3. LCM (White 9 AVG 1/9) :
Brightness: 400/m² (TYP)
Uniformity:80%(MIN)
4. OPERATING TEMP: -20° C TO 70° C, STORAGE TEMP: -30° C TO 80° C
5. * Critical Parameter, () ref Parameter, [] cpk Parameter
Unspecified Tolerances:±0.20mm
Modification mark:
6. REQUIREMENTS ENVIRONMENTAL PROTECTION: RoHS

Limits Unless Otherwise Noted				Signature	Date	Material		4D SYSTEMS PTY LTD	
Tolerance Grade				Design		Unit	mm		
Grade	○			Drawing		Scale	1:1	Customer NO.	
0 - 150	±0.10	±0.15	±0.20	Check		Date	20251119	Drawing NO.	4DHDMI-054-1080-1920-C
150+	±0.20	±0.25	±0.30	Approval		Projection		Ver.	1.0
Angle	±0.50°	±0.80°		Customer confirm					