

2 Port USB VGA Cable KVM Switch - USB Powered with Remote Switch

Product ID: SV211USB



The SV211USB 2-Port VGA Cable KVM Switch lets you control two VGA, USB-equipped PCs with a single monitor, keyboard and mouse.

To help organize your desk without sacrificing valuable work space, this VGA USB KVM switch features a compact footprint and integrated KVM cables that can be connected directly to your systems. Plus, the KVM is USB-powered, eliminating the need for a bulky external power adapter and wall outlet.

This VGA KVM switch offers support for resolutions up to 2048x1536, for the ability to drive a high-resolution VGA display. For simple switching between connected systems, the KVM features a convenient push-button remote switch on a 1.5 meter (5ft) cable, as well as keyboard hot-key support and PC or Mac® compatible switching software.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations, increasing user productivity in the office

Features

- Supports resolutions up to 2048x1536
- Switch PCs via push-button, hot-keys or switching software (included)
- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac® platforms
- USB Powered - No external power adapter required
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable

Hardware	Warranty	2 Years
	Audio	No
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	No
Performance	Hot-Key Selection	Yes
	IP Control	No
	On-Screen Display	No
	Port Selection Support	Push Button, Hotkeys, and Software
Connector(s)	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	1 - VGA (15 pin, High Density D-Sub) Male 1 - USB Type-A (4 pin) USB 2.0 Male
Software	OS Compatibility	Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016 Mac OS 10.x (Tested up to 10.9), 9.x
Special Notes / Requirements	Note	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
Indicators	LED Indicators	1 - PC Selection indicator
Power	Power Source	USB-Powered
Environmental	Humidity	0~90% RH Non-Condensing
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (4°F to 140°F)
Physical Characteristics	Cable Length	33.5 in [850 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.9 in [23 mm]
	Product Length	3.5 in [88 mm]

	Product Weight	11.3 oz [321 g]
	Product Width	2.6 in [66 mm]
Packaging Information	Shipping (Package) Weight	15.4 oz [435 g]
What's in the Box	Included in Package	1 - KVM Switch 1 - Software CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.