

Professionally approved products.
 Datasheet
 New Link 24 port Switch

RS Stock number 794-7079



Notification	
Product Code	NLHUB-924A
Short Description	NEWlink 24 port 10/100 dual speed switch
Full Description	The NLHUB-924A is a 24 port Ethernet switch. This product would be ideal at the heart of all networking systems with its fast speeds of 10/100Mbps and its automatic MAC learning capabilities. The NLHUB-924A comes with a standard 1U 19-inch rack mountable steel case which enables an optimum number of ports while only taking up minimal space.
Extra Information	Specification Complies with IEEE802.3, IEEE 802.3u standards 24 port 10/100 Mbps Auto-Negotiation RJ45 ports supporting Auto-MDI/MDIX Supports IEEE 802.3x flow control for Full Duplex and Half Duplex modes Supports MAC address auto-learning and auto-aging Expandable by cascading more hubs together LED indicators for monitoring power, link, activity, 100Mbps Standard 19-inch rack-mountable steel case Internal universal power supply