
KEMET Part Number: SMR15225J63B12L16.5CBULK

(F211BM225J063ALG5C)



SMR/F211, Film, Metallized PPS, General Purpose, 2.2 uF, 5%, 63 VDC, 125°C, Lead Spacing = 15mm



General Information	
Supplier:	KEMET
Series:	SMR/F211
Dielectric:	Metallized PPS
Style:	Radial
Features:	Audio Applications
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	The rated voltage decreases 2%/ C between +125C and +150C
Notes:	Case Size = BM

Dimensions	
L	18mm MAX
Н	15mm MAX
Т	8mm MAX
S	15mm +/-0.4mm
LL	16.5mm +0.5mm
F	0.8mm +/-0.05mm
G	0.5mm NOM

Specifications	
Capacitance:	2.2 uF
Capacitance Tolerance:	5%
Voltage AC:	40 VAC
Voltage DC:	63 VDC
Temperature Range:	-55/+150C
Rated Temperature:	125°C
Dissipation Factor:	0.15% 1kHz, 0.35% 10kHz
Insulation Resistance:	2.27273 GOhms
Max dV/dt:	6 V/us

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	400

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

