

Screwdriver - SF-BIT-SL 0,45X2,4-70 - 1212607

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screw bit, slotted, E6.3-1/4" drive, size: 0.45 x 2.4 x 70 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 046356 620482
GTIN	4046356620482
Weight per Piece (excluding packing)	7.980 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	70 mm
Width (a)	26 mm
Blade thickness	0.4 mm
Blade width	2 mm
Blade height	60 mm

General

Type	Bladed
Material	Steel
Test standard	DIN/ISO 2380-1 IEC 60900:2004
Weight	18 g

Standards and Regulations

Test standard	DIN/ISO 2380-1 IEC 60900:2004
---------------	-------------------------------

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Screwdriver - SF-BIT-SL 0,45X2,4-70 - 1212607

Classifications

eCl@ss

eCl@ss 10.0.1	21044204
eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040400
eCl@ss 6.0	21049200
eCl@ss 7.0	21044204
eCl@ss 8.0	21044204
eCl@ss 9.0	21044204

ETIM

ETIM 4.0	EC002115
ETIM 5.0	EC002116
ETIM 6.0	EC002116

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01750
-----	--	--------------------------