

Features

- Super bright 900 lumen
- Beam range up to 82 metres
- K07 shock proof
- Smart memory – remembers last mode used
- USB-C rechargeable

RS PRO LED Head Torch, 900 lm

RS Stock No.: 0143259



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Professional LED Headtorch

900 lumen white Cree LED, 6500k
Wide angle light spread with bright central spot
72° rotational head
Smart Memory function - remembers last mode used
Useful battery level and charging indicator
IPX5 water resistant
IK07 shock proof - 2m drop resistant
USB Type-C 5V 1A charging - 4.5 hour charge time
1m high quality charging cable included

Ideal for inspection work providing hands free illumination this feature-packed head torch allows you to illuminate dark areas hands-free whilst delivering great performance.

General Specifications

Rechargeable	Yes
Lamp Type	LED
Luminosity	900 lm
Hazardous Area	No
Beam Type	Long distance beam with wide spread
Weight with Batteries	188g
Colour	Red/Black
Case Material	ABS

Mechanical Specifications

USB	Type-C 5V 1A charging
Battery Charge Time	4.5 hours
Cable	1m charging cable included
Battery	3.7v 18650 2600mAh Li-ion battery
Dimensions	Headtorch W44 x H39 x D46mm Battery pack: W86 x H36 x D37 mm
Weight	188g (including battery & headbands)
Operation	Switch Sequence: HIGH - 900LM - 3.5hrs > MID - 340LM - 9hrs > LOW - 30LM - 100hrs > OFF SMART MEMORY FUNCTION:- If left ON in any mode for 5 seconds or more, the next press will turn OFF. Next press ON will return to last mode used.

Approvals

Declarations	EMC RoHS REACH
Standards Met	EN IEC 55015:2019/A11:2020 EN 61547:2009 EN 61000 3-2:2014 EN 61000 3-3:2013 IEC 62321 IPX5 IEC 62133

Similar Products

Stock No.	Brand	Product Name	Luminosity	Rechargeable	Mains Plug
0143259	RS PRO	LED Head Torch	900 lm	Yes	USB
239-7020	RS PRO	LED Head Torch	320 lm	Yes	USB
200-6746	RS PRO	LED Head Torch	350 lm	Yes	USB
239-7022	RS PRO	LED Head Torch	420 lm	Yes	USB
255-4198	RS PRO	LED Head Torch	300 lm	Yes	USB
186-4622	RS PRO	LED Head Torch	450 lm	Yes	USB
219-8133	RS PRO	LED Head Torch	350 lm	Yes	USB
239-7017	RS PRO	LED Head Torch	400 lm	Yes	USB
255-4200	RS PRO	LED Head Torch	800 lm	Yes	USB
186-4621	RS PRO	LED Head Torch	250 lm	Yes	USB
176-6031	RS PRO	LED Head Torch	300 lm	Yes	USB
219-8135	RS PRO	LED Head Torch	815 lm	Yes	USB
219-8134	RS PRO	LED Head Torch	575 lm	Yes	USB