



PRODUCT DATASHEET

Datasheet creation date: 2025/07/08 2:20 (UTC)



6203DDU

Single-Row Deep Groove Ball Bearings



Boundary Dimensions

d	17	mm	Bore diameter
D	40	mm	Outside diameter
B	12	mm	Width
r (min.)	0.6	mm	Chamfer dimension

Basic Load Ratings

Cr	10500	N	Basic dynamic load rating
C0r	4800	N	Basic static load rating

Speeds

Grease	12000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	21	mm	Diameter of shaft abutment
da (max.)	23.5	mm	Diameter of shaft abutment
Da (max.)	36	mm	Diameter of housing abutment
ra (max.)	0.6	mm	Radius of shaft or housing fillet

Calculation factors

fo	13.2		Factor
----	------	--	--------

Additional information

z	8		Number of Balls
Dw	6.747	mm	Ball Diameter

Mass

Mass approx.	0.067	kg	Mass approx.
--------------	-------	----	--------------

