

Hybridcbl. Papst LAiO20 HD 0,5m



Image is for illustration purposes only. Please refer to product description.

Part number	61 88 720 0026 0050
Specification	Hybridcbl. Papst LAiO20 HD 0,5m
HARTING eCatalogue	https://harting.com/618872000260050

Identification

Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 Female 12 + 3 poles
Connector 2	LP 14 + 3 poles
Type of cable	Copper cable (round)
Description of the cable	Oil resistant Halogen-free Silicone-free
Features	Highly flexible Drag chain compatible

Version

Cable length	0.5 m
Core structure	3x 1.5 mm ² + 2x 0.34 mm ² + 2x 2x 0.22 mm ²
Field of application	for hybrid function

Termination data

Nominal voltage	60 V DC
-----------------	---------

Technical characteristics

Limiting temperature	-20 ... +80 °C unmoved -20 ... +80 °C moved
----------------------	--



Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black

Specifications and approvals

Specifications	IEC 60332-1 Flame retardancy
----------------	------------------------------

Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140274471
eCl@ss	27060490 Ready-made low-voltage line (unspecified)
ETIM	EC002587
UNSPSC 24.0	26121629