

## FEATURES

- **Polycarbonate construction:** Offers high durability and resistance to impact, ensuring long-term use in industrial settings.
- **Accommodates 2 padlocks:** Provides secure storage for up to two padlocks, enhancing safety management.
- **Compact dimensions:** With a depth of 34 mm, height of 469.9 mm, and width of 444.5 mm, it fits easily into various spaces without compromising on storage capacity.
- **Dual colour options:** Available in red and white, allowing for easy identification and integration into existing safety systems.
- **ISO certified:** Complies with ISO 9001, ISO 14001, and OHSMS 45001 standards, ensuring quality and environmental management.
- **UKAS accredited:** Certified by UKAS 0043, providing assurance of compliance with safety and quality standards.

## RS PRO 2 Padlock Tag Station, Polycarbonate

RS Stock No: 694-398



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO Tag Station is designed to provide a secure and organised solution for managing safety tags and padlocks in industrial environments. With a robust polycarbonate construction, it ensures durability and reliability in demanding conditions. This tag station is ideal for maintaining safety compliance and improving workflow efficiency.

## General Specifications

|                    |             |
|--------------------|-------------|
| Colour             | Red, White  |
| Number of Padlocks | 2           |
| Product Type       | Tag Station |

## Mechanical Specifications

|          |               |
|----------|---------------|
| Depth    | 34 mm         |
| Height   | 469.9 mm      |
| Material | Polycarbonate |
| Width    | 444.5 mm      |

## Approvals

|                     |   |
|---------------------|---|
| Standards/Approvals | ISO 9001, ISO 14001, OHSMS 45001, UKAS 0043 |
|---------------------|---|