



**Part Number :** [1201080036](#)

**Product Description :** Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, Teal PVC Cable, 20.0m (65.62') Length

**Series Number :** 120108

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Number :** E11A06002M200



---

## Documents & Resources

### Drawings

[1201080036\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)4578-DC (25 June 2020)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120108
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, Teal PVC Cable, 20.0m (65.62') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78678889589

### Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

### Physical

Cable Diameter	6.35mm (.250")
Cable Length	20.0m (65.62')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded

Gender	Male-Male
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	869.500/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +75°C
Wire/Cable Type	Unshielded PVC
Wire Size (AWG)	24