



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Rotary head
Product compatibility	XC2J
Associated lever	ZC2JY12 ZC2JY51 ZC2JY31 ZC2JY91 ZC2JY13 ZC2JY11 ZC2JY81
Associated body	ZC2JC15 ZC2JC25
Movement of operating head	Rotary
Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	From left and right CW and CCW
Positive opening	Without
Net weight	0.21 kg
Head material	Metal

Environment

Ambient air temperature for operation	10... 120 °C
Ambient air temperature for storage	10... 120 °C

Environmental characteristic	High temperature
------------------------------	------------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------