



Figure similar

SIMATIC ET 200SP HA, Carrier module in single carrier for holding one interface module of the ET 200SP HA incl. server module

General information	
Product type designation	IM carrier module, single
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; Asset data
Supply voltage	
Rated value (DC)	24 V
Hardware configuration	
Slots	
<ul style="list-style-type: none"> Number of slots 	1
Potential separation	
between backplane bus and supply voltage	Yes
Isolation	
Isolation tested with	1 500 V DC/1 min, type test
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. horizontal installation, max. vertical installation, min. vertical installation, max. 	-40 °C 70 °C -40 °C 60 °C
Dimensions	
Width	100 mm
Height	204 mm
Depth	35 mm; measured without power plug
Weights	
Weight, approx.	250 g
Classifications	

	Version	Classification
eClass	14	27-24-26-07
eClass	12	27-24-26-07
eClass	9.1	27-24-26-07
eClass	9	27-24-26-07
eClass	8	27-24-26-07
eClass	7.1	27-24-26-07

eClass	6	27-24-26-07
ETIM	10	EC001603
ETIM	9	EC001603
ETIM	8	EC001603
ETIM	7	EC001603

Approvals / Certificates

General Product Approval



[Miscellaneous](#)



[China RoHS](#)



General Product Approval

For use in hazardous locations



[Declaration of Con-
formity](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)



Maritime application

Environment



[NK / Nippon Kaiji Ky-
okai](#)



[CCS \(China Classifica-
tion Society\)](#)

Siemens
EcoTech



last modified:

10/23/2025