

53753

Tube Brush, 480 mm, Hard, Blue



The smallest diameter of the tube cleaners is used to clean small pipes and very narrow spaces between machine parts. The filaments are attached to a twisted stainless steel rod which makes chemical resistant and strong. Example of use; sausage filler tubes.

Technical Data

Item Number	53753
Visible bristle length	3 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	2550 Pcs
Quantity Per Layer (Pallet)	150 Pcs.
Box Length	525 mm
Box Width	150 mm
Box Height	105 mm
Product Diameter	10 mm
Length	480 mm
Width	22 mm
Height	22 mm
Gross Weight	0,086 kg
Net Weight	0,073 kg
Cubik metre	0,0002 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020537530
GTIN-14 Number (Box quantity)	15705020537537
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact