



ENGLISH

Datasheet

RS Pro 10 Piece Screwed Shank Slot Drill Set BS 122/4

RS Stock No: 1857557



Specifications:

2 Flute Screwed Shank Slot Drills

Centre Cutting

BS 122/4

High Speed Steel: M35 with 5% Cobalt

10 Piece Set Contains:

4mm, 5mm, 6mm, 8mm, 10mm, 12mm, 14mm, 16mm, 18mm & 20mm

Order Code	Product Description
1857557	Screwed Shank Slot Drill Set 10 Piece Set



ENGLISH

Datasheet

RS Pro 10 Piece Screwed Shank Slot Drill Set BS 122/4

Technical Specifications:

Code	Dia mm	Flute Lgth	O/A Lgth.	Shank Dia
1-040	4.0	9.5	52.5	6.0
1-050	5.0	9.5	52.5	6.0
1-060	6.0	11.0	56.5	6.0
1-080	8.0	12.5	59.5	10.0
1-100	10.0	14.5	60.5	10.0
1-120	12.0	19.0	66.5	12.0
1-140	14.0	22.0	68.5	12.0
1-160	16.0	22.0	72.0	16.0
1-180	18.0	24.0	74.0	16.0
1-200	20.0	25.5	77.0	16.0