

FEATURES

- Quick and easy to install
- 2m length
- Ideal for clean cable management.
- Open slotted
- Breakpoints on bars and channel floor

RS PRO Grey Slotted Panel Trunking - Open Slot, W30 mm x D40mm, L2m, PVC

RS Stock No.: 136-9104



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the great value brand RS PRO, comes a range of high quality grey slotted cable trunking. Manufactured out of lead-free and flame retardant PVC this rigid trunking has been designed to allow the user to fix it to the area it will be applied to, allowing for a simple yet effective installation and secure cable organisation

General Specifications

Trunking/Chain Type	Slotted Panel Trunking
Material	PVC
Colour	Grey
Fire Behaviour	Self-extinguishing
UV Resistance	PVC is conditionally permanent to UV- light, changes in colour under UV light cannot be excluded
Angle	90°
Applications	Electrical workshops, Offices and indoor work spaces, Schools, Hospitals and Hotels

Mechanical Specifications

Length	2m
Width	30mm
Depth	40mm
Slot Type	Open
Dielectric Strength	>30kV/mm

Operation Environment Specifications

Operating Temperature Range	-20°C to 60°C
-----------------------------	---------------

Approvals

Standards Met	CE, CULus Recognised, DIN EN50085, EN45545 HL2, GL, VDE 0472
---------------	--

