



PISTOL-SHAPED RUST-REMOVER - 3000 CPM - 19 NEEDLES RC4115

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:52





DESCRIPTION

PISTOL-SHAPED RUST-REMOVER - 3000 CPM - 19 NEEDLES

Rust-remover designed for general maintenance. Dual-function because it can also be used as a chipper. Economic solution, suitable for all surface preparation and weld bead treatment jobs. Can also be used in the construction sector. Control lever. Sheathed handle.

STANDARDS / DIRECTIVES

2006/42/CE, ISO 11148-6, ISO 15744, ISO 28927-2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:52



SPECIFIC DATA

Designation	PISTOL-SHAPED RUST-REMOVER - 3000 CPM - 19 NEEDLES
Sales reference	RC4115
L (mm)	342
Weight (g)	3400
l (mm)	70
h (mm)	185
Piston stroke mm	73
Fitting (mm)	23.5
Vibration (m/s²)	13
Noise level (dBa)	94
C mm	6,3
C min mm	240
C mm	1/4
C mm	3 000
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:52

