

Hot air tool - Professional Line

mobile heat MH 3

including rechargeable battery and charger
EAN 4007841 066604



Function description

Mobile. Fast. Precise. mobile heat MH3, the 18 V cordless hot air tool with 2 temperature settings (300°C/500°C). Heats up to 300°C in a maximum of 5 seconds. High-performance, with an airflow rate of up to 200 l/min. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case (upon request, with CAS rechargeable battery and charger).

Technical specifications

Temperature	300 – 500 °C
Airflow rate	200 l/min
Motor, type	Brush motor
Function, life expectancy, motor	500 h
Temperature setting	2-stage
Temperature display	LED segment display
Power supply, detail	Rechargeable lithium-ion battery
Heating element	Ceramic heating element
Loc function	No
Residual heat indicator	No

Function, hanger	Yes
Replaceable heating element	No
Thermal cut-out	Yes
Thermostat	No
Dimensions (L x W x H)	225 x 72 x 204 mm
Rechargeable battery voltage	18 V
Mains power supply	18 V
PU1, net weight	2,21 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841066604

Accessories

EAN 4007841 065560	CAS Battery 18V 8.0Ah
EAN 4007841 065584	CAS Charger SC 18-55