



ANSMANN Home Charger 230PD with cable

Smart USB charger with integrated cable and 30 W for smartphones, tablets and other USB devices

Features

- USB charger with 2 USB ports (USB-A and USB-C) and 30 W output
- Integrated USB-C charging cable with semi-automatic cable pull
- Intelligent charge controller ensures optimum charging
- Multisafe technology protects both your end-device and the charger
- Suitable for devices that can be charged or operated via USB
- Input: 110 - 240V AC wide-range input enables worldwide use



Article number: 1001-0186

Product content: Home Charger 230PD with cable, manual



Specifications

Output voltage	5V DC			
Input voltage	110 - 240V AC			
Max. output current	3 A			
Max. input current	0.85 A			
Charging currents	Mode	Voltage range	Max. current	Max. power
	USB-C	5,0 V DC	3,0 A	15,0 W
	USB-C	9,0 V DC	3,0 A	27,0 W
	USB-C	12,0 V DC	2,5 A	30,0 W
	USB-A	5,0 V DC	3,0 A	15,0 W
	USB C + Kabel	5 V DC	3,0 A	15,0 W
	USB C + USB A	5 V DC	3,0 A	15,0 W
	USB A + Kabel	5 V DC	3,0 A	15,0 W
	USB-A + USB-C + Kabel	5 V DC	3,0 A	15,0 W
	PPS	5 - 11 V DC	3,0 A	33,0 W
	USB-A	9 V DC	2,0 A	18,0 W
	USB-A	12 V DC	1,5 A	18,0 W
USB-Ports	2			
Port	USB-A / USB type C			
Maximum power	30 W			
Average operational efficiency	86,6 %			
Efficiency at low load	83,5 %			
Power consumption at no load	0,100 W			
Charging protocol	Power Delivery Profile 2 / Power Delivery Profile 3 / PPS / Quick Charge 2.0 / Quick Charge 3.0 / Quick Charge 4.0			

Color	white
Packaging	cardboard box
Operating temperature	-20 - 35 °C
Storage temperature	-25 - 70 °C
Dimensions	0 × 0 × 0 mm