

# PA901435 CRIMPER PZ6 ROTO

A professional-quality rotary crimping tool for insulated and non-insulated wire ferrules. The rotating die design enables both front-load and side-load ferrule insertion in a single tool without die changes. Crimps conform to EN 60947-1 & DIN 46228 Pt. 1 and 4.

## CRIMPING RANGE

24-10 AWG (0.25-6.0 mm<sup>2</sup>)

## FEATURES:

- Rotating die for front or side ferrule insertion
- Single tool covers full 24-10 AWG range — no additional dies required
- Crimps conform to EN 60947-1 & DIN 46228 Pt. 1 and 4
- Hardened steel die system for long life
- Durable steel construction
- Ergonomic handles for low-effort operation

Weight:

2 lbs



Paladin® brand hand tools from Tempo® Communications carry a Limited Lifetime Warranty.

1390 Aspen Way Vista, CA • 92081 PA901435 04/26

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927050

©2026 Tempo Communications Inc. • An ISO 9001 Company

EMEA Office: Tempo Europe Limited

Brecon House • William Brown Close • Cwmbran • NP44 3AB • UK

[TempoCom.com](http://TempoCom.com) | tel 800.642.2155 | [sales@tempocom.com](mailto:sales@tempocom.com)



**TEMPO**  
COMMUNICATIONS

*Renewed Vision. Innovation Forward.*



Follow us on Social Media  
[@TempoComms](https://www.instagram.com/TempoComms)