



(0.50 mm) .0197"



RIGHT-ANGLE GROUND PL

SPECIFICATIONS


For complete specifications and recommended PCB layouts see www.samtec.com?QTH-RA or www.samtec.com?QTH-DP-RA


Insulator Material: Black Liquid Crystal Polymer Terminal Material: Phosphor Bronze Weld Tab: Phosphor Bronze Ground Plane: Phosphor Bronze Plating: Au or Šn over 50 μ" (1.27 μm) Ni **Current Rating:** Contact: 2.2 A per pin (2 pins powered) Ground Plane: Ground Plane: 21.8 A per ground plane (1 ground plane powered) Operating Temp Range: -55 °C to +125 °C Voltage Rating: 220 VAC RoHS Compliant:

PROCESSING

Lead-Free Solderable: SMT Lead Coplanarity: (0.10 mm) .004" max (020-090)

Board Mates:





Some lengths, styles and options are non-standard, non-returnable.