



ENGLISH

Datasheet

Stock No: 235-736

RS Pro P14.5s Halogen Bulb, Clear, 12 V



Product Details

Flashing Filament Beacons

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.

Approximately 80 flash per minute

60W light output where bulb is supplied

High protection rating of IP56

Optional cage guard for three point mount versions

Surge protection for safety against peak voltage

Full internal suppression for maximum interference reduction

166mm diameter

Three point mounting



ENGLISH

Note

Lens must be purchased separately

Supplied with

Bulb (except 12/24V versions)

Specifications:

Voltage Rating	12 V
Bulb Type	Halogen
Lamp Base	P14.5s
Lens Colour	Clear
Diameter	166 mm